

# Hear like no other

Inspired by the ReSound philosophy of Organic Hearing, ReSound ONE™ with the groundbreaking\* M&RIE (Microphone and Receiver-In-Ear) delivers an immersive and individualized hearing experience with greater depth and direction.

ReSound ONE adapts to patients' needs in all areas, including a new modern design, palette of colors, audio streaming from iOS® and Android™ devices, and the best rechargeable battery life in the industry for more than a full day of worry-free use.

## RIE STYLES



## RIE COLORS




### THE MOST NATURAL SOUND QUALITY IN AN RIE HEARING AID



M&RIE combines the two traditional microphones with a third that sits discreetly inside the ear canal as an integrated part of the receiver module. Made possible by a brand new sound processing chipset and feedback management system, DFS Ultra III, this previously unachievable breakthrough uses the unique shape of the ear to collect sound the way nature intended.

### GREATER HEARING IN ANY ENVIRONMENT



All Access Directionality automatically adjusts directional microphone patterns based on the environment so patients can hear what's important and still monitor the sounds around them. In noisier situations, All Access Directionality utilizes a new binaural connection to create a stronger, more focused beam for sounds in front, providing up to **2 dB better signal-to-noise ratio\*\***.

### THE BEST 1:1 HEARING EXPERIENCE IN THE TOUGHEST ENVIRONMENTS



User-controlled Ultra Focus uses a powerful directional pattern to help your patients focus on the person in front of them in very noisy environments with up to **30% improvement in speech understanding\*\*\***. By using the speech frequencies for targeted directionality and the high and low frequencies to monitor the environment, they can hear speech and still maintain spatial cues from the sides and back.

### UNMATCHED RECHARGEABILITY AND CONNECTIVITY

ReSound ONE offers an industry-leading rechargeable solution with up to 30 hours† of battery life or 25 hours with unlimited streaming. It adapts to patients' lifestyles by connecting them to the world around them with direct audio streaming via future-proof Bluetooth Low Energy. Access to the ReSound Smart 3D™ app and a versatile range of wireless accessories gives them even more options to connect to the sounds they enjoy everyday.



\*Microphone in ear and two standard directional microphones, directionality features, wireless audio streaming.


\*\*Compared to traditional directionality. Groth J. (2020). The evolution of the binaural hearing strategy: All Access Directionality and Ultra Focus.

\*\*\*Compared to All Access Directionality. Groth J. (2020). The evolution of the binaural hearing strategy: All Access Directionality and Ultra Focus.

†Expected battery life depends on active features, the use of wireless accessories, hearing loss, device age and sound environment.

## DESIGNED FOR ULTIMATE COMFORT, DISCRETION AND PERFORMANCE

The modern design has just one touchpoint on the back of the ear and sits lower for greater discretion and comfort. The new receiver design with Automatic Receiver Detection in ReSound Smart Fit and enhanced dome security makes it easier to fit and more comfortable for your patients to wear. For added flexibility, two different charger options serve as stylish, portable and protective cases, ideal for traveling and storage.



## ACCURATE, COMFORTABLE AND INDIVIDUALIZED FROM THE FIRST FIT AND BEYOND

The new, personalized feature prescriptions in ReSound Smart Fit are guided by peer-reviewed research on how to optimize advanced sound processing features to give you a better starting point with ReSound ONE's feature settings. It can help decrease the need for fine-tuning, from the first fit and beyond. Adjustable gain percentage helps you create the most comfortable first fit for your patients for higher patient satisfaction.

Discover more at [pro.resound.com](http://pro.resound.com)

### Manufacturer according to FDA:

**GN ReSound North America**  
8001 E Bloomington Freeway  
Bloomington, MN 55420  
USA  
1-800-248-4327  
[pro.resound.com](http://pro.resound.com)

### Manufacturer according to Health Canada:

**ReSound Canada**  
2 East Beaver Creek Road, Building 3  
Richmond Hill, ON L4B 2N3  
Canada  
1-888-737-6863  
[pro.resound.com](http://pro.resound.com)

MODEL*	RT961-DRW RT961-DRWC RT962-DRW
<b>DEVICE CONFIGURATIONS</b>	
Battery size	61-DRW: 312 Zinc-Air 61-DRWC: Lithium-Ion 62-DRW: 13 Zinc-Air
IP Classification	IP68
Receiver Options	LP, MP, HP, UP and M&RIE
<b>AUDIOLOGICAL FEATURES</b>	
WARP compression (WDRC) - number of channels	17
All Access Directionality	●
M&RIE Receiver Compatibility	●
Ultra Focus	●
Synchronized Soft Switching	●
Environmental Optimizer II	●
Noise Tracker II	5 settings
Expansion	3 settings
Impulse Noise Reduction	3 settings
Wind Guard	3 settings
Sound Shaper	●
DFS Ultra III (w/ Music Mode)	●
Synchronized Acceptance Manager	●
Tinnitus Sound Generator	●
<b>FUNCTIONAL FEATURES</b>	
Ear-to-Ear Communication	●
Direct Audio Streaming	●
ReSound Wireless Accessory Compatibility	●
ReSound Smart 3D™ app	●
<b>RESOUND ASSIST</b>	
Live Assistance	●
Remote Fine-Tuning	●
Remote Firmware Updates	●
<b>FITTING FEATURES</b>	
Fitting Software Smart Fit 1.8 or higher	●
Max Gain Handles	17
Fully Flexible Programs	4
Datalogging	●
Automatic Receiver Detection	●
Noahlink Wireless	●
* View the datasheets for information on RT761-DRW, RT761-DRWC, RT762-DRW, RT561-DRW, RT561-DRWC and RT562-DRW.	



Standard Charger



Premium Charger

