

Cable and Wireless Fitting Guide

ReSound Smart Fit™							
	20310800 (Noahlink Wireless)	9022 907 69019 (HI-PRO CABLE/RIGHT/CS44) 9022 907 69029 (HI-PRO CABLE/LEFT/CS44) 3122 150 73781 (FLEX CONNECTOR CLIP CS63) 19181700 (STRIP,FLEX,CS63,PRG)	15206700 (Programming cable CS63, Right) 15206701 (Programming cable CS63, Left) 19181700 (STRIP,FLEX,CS63,PRG)	9022 907 69019 (HI-PRO CABLE/RIGHT/CS44) 9022 907 69029 (HI-PRO CABLE/LEFT/CS44) 19533900 (ADAPTER,FLEX,3 PIN,CS53)	9022 907 69019 (HI-PRO CABLE/RIGHT/CS44) 9022 907 69029 (HI-PRO CABLE/LEFT/CS44) 19902500 (PROGRAMMING ADAPTOR 2)	18523700 (IIC 10A PROG PILL CABLE, LEFT) 18523800 (IIC 10A PROG PILL CABLE, RIGHT)	9022 907 69019 (HI-PRO CABLE/RIGHT/CS44) 9022 907 69029 (HI-PRO CABLE/LEFT/CS44) 19215000 (KIT,PROG,SUPER POWER, LO90)
ReSound LiNX Quattro							
RIE WL - REx62	•				•		
RIE WL - REx61	•						
Custom WL	•	•	•	•			
ReSound LiNX 3D™							
RIE WL - LTx62	•				•		
RIE WL - LTx61	•	•	•	•			
BTE WL - LTx77, LTx88	•				•		
BTE WL - LTx67	•	•	•	•			
Custom WL	•	•	•	•			
Custom non-WL		•	•	•			
Custom IIC						•	
ReSound ENZO 3D							
BTE WL - ETx98	•						•
BTE WL - ETx88	•				•		

Please note:

Products supported in ReSound Smart Fit do not support the Airlink dongle.
 ReSound hearing instruments for both wireless and non-wireless **fittings require a fresh battery when fitted with ReSound Smart Fit.**
 Does not apply for RIE WL REx61, which comes with an in-built lithium-ion battery.

